D SUB IP 67 MA ANG_PCB_37P_S4_METAL FRAM

Spotted an error? | Print page | Back

Image is for illustration purposes only. Please refer to product description.

Login to MyHARTING
for pricing and stock check

Quantity: 100

Shopping cart

Email inquiry

Catalogue
HARTING Device Connectivity - Page 378

Browse
Download

- Features
- Connection data
- Dimensions and weight
- Supplements

Part number:	09 67 637 7658
Description:	D SUB IP 67 MA ANG_PCB_37P_S4_METAL FRAM

Features

Application:	Board Connector Panel Mount
Class of Protection:	IP67
Contact Pitch:	2.54 mm
Gender:	Turned Male Contact
Mating Hardware:	Flange Thread 4-40
No. of contacts:	37
Performance level:	S4
RoHS conformity:	Yes
Termination Type:	Solder
Type:	Rear Mount Angled Metal Frame

Top

Connection data

Current:	5 A @ 20°C

Top

Dimensions and weight

Net Weight:	163 g

Top

Supplements

Series:	D-Sub Waterproof

Top

Downloads

Title	Download
CAD data 3D	STEP
CAD data 3D	JT
HARTING Device Connectivity - Page 378	PDF

Recently viewed - Delete

D SUB IP 67 MA STR_PCB_25P_S4_METAL FRAM
Show product details

D SUB IP 67 MA ANG_PCB_25P_S4_METAL FRAM
Show product details

D SUB IP 67 MA ANG_PCB_25P_S4_METAL FRAM
Show product details

D SUB IP 67 FE ANG_PCB_25P_S4_METAL FRAM
Show product details

D SUB IP 67 MA STR_PCB_15P_S4_METAL FRAM
Show product details

D SUB IP 67 MA ANG_PCB_15P_S4_METAL FRAM
Show product details

D SUB IP 67 FE STR_PCB_15P_S4_METAL FRAM
Show product details

D SUB IP 67 FE ANG_PCB_15P_S4_METAL FRAM
Show product details

D SUB IP 67 MA STR_PCB_15P_S4_METAL FRAM
Show product details

D SUB IP 67 MA ANG_PCB_15P_S4_METAL FRAM
Show product details

Recently searched

No searches have been done yet.

Downloaded from Arrow.com.