Johanson Part Number LRW0603WJ68NGG001E

Johanson Part Number: LRW0603WJ68NGG001E	Johanson Company: JTI
Legacy P/N: L-14W68NJV4E	Size for Capacitors (EIA): None
Description: WireWound Inductors, 0603, 68nH±5%, 600mA, Ni/Au (RoHS), No Mark, 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.049
Schedule B: 8504.50.40.00	Thickness (Min): 0.033
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.018
RoHS Compliance: Yes, RoHS 10/10	Standard Item: Yes
REACH: Yes	Lead Time Typical (Weeks)*: 18
Country of Origin: MY	Length (Min): 0.055
Product Family: Inductors	Length (Max): 0.071
Product Subfamily: WireWound Inductors	Width (Min):0.033
Capacitance Value: None	Width (Max): 0.049
Cap Unit of Meas: None	Part Weight (mg): 4.90
Tolerance: ±5%	Packaged Width (lb) Arm: 0.35
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 3000
Termination: 0	Operating Temp Range: -40°C to +125°C
Marking: No Mark	Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%
Product Release Date: Jan. 13, 2006	Storage Temp Range (None Operating): -40°C to +125°C
Harmonization: 8504.50.40.00	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: https://www.johansontechnology.com/wirewound-inductors

Printed from: https://www.johansontechnology.com/part/LRW0603WJ68NGG001E/

Downloaded from Arrow.com.