

SEARCH KEYWORD, PART NUMBER
 🔍



Part Number: **13706547**

Product Name: [GT 150 Series](#)

8 Way Female GT FBT 1.5 Sealed Connector

[Share](#)
[Print](#)
[Contact Us About This Item](#)

This part is not currently offered in our sample program.

SEND REQUEST
 →


Request this part be added to the sample program.

[ATTRIBUTES](#)
[DOCUMENTS](#)
[ECAD](#)
[COMPATIBLE PARTS](#)


Attributes

Product Family GT	Height (mm) 28.17
Product Series 150 Series	Color BLACK
Max. operating temperature +125°C	Primary Locking Mechanism CAVITY LOCK
Min. operating temperature -40°C	Weight (g) 9.81777
No. of Ways 8	Terminal 1 Size 1.5
Cable Exit Orientation 180°	Sealing Sealed
Gender Female	Primary Material PBT
Length (mm) 27.5	Coding/Index 101
Width (mm) 32.97	


Other Products



**35829171**  
 2 Way Male 0.5 Unsealed Green




**35829170**  
 2 Way Male 0.5 Unsealed Violet



**35829169**  
 2 Way Male 0.5 Unsealed Blue



Next Steps



Keep pace with  
where mobility is  
going.

See what's next and get the latest  
updates.

SIGN UP TO GET  
UPDATES
 →

Don't worry. We won't flood your inbox or share your email.

INSIGHTS

[EXPLORE ALL ARTICLES](#)  
[CASE STUDIES](#)  
[MOBILITY INSIDER](#)  
[RESEARCH PUBLICATIONS](#)  
[WHITE PAPERS](#)

SOLUTIONS

[Advanced Safety](#)  
[Connected Services](#)  
[Connection Systems](#)  
[Connectivity and Security](#)  
[Electrical Distribution Systems](#)  
[Middleware & DevOps](#)  
[Smart Vehicle Architecture](#)  
[User Experience](#)  
[Vehicle Electrification Systems](#)  
[HellermannTyton](#)  
[Intercable Automotive Solutions](#)  
[Motional](#)  
[Winchester Interconnect](#)  
[WInd River](#)

CATALOG

ABOUT

[Our Mission](#)  
[Our Businesses](#)  
[Our Locations](#)  
[Our Foundation](#)  
[Sustainability](#)  
[Suppliers](#)

PRIVACY

[Terms of Use](#)  
[Cookie Policy](#)

LEGAL &  
COMPLIANCE

CAREERS

[INVESTORS](#)  
[NEWSROOM](#)  
[CONTACT](#)