TRACO POWER

Inductor

TCK-044

Order Code	TCK-044
Inductance	3.3 µH ±20% (at 1 kHz / 1 V)
Impedance (DCR)	60 mΩ max.
Rated Current	2 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-044



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	5.2 ±0.5
B	5.8 ±0.5
C	5.2 max.
D	1.3 typ.
E	5.5
F	2.15
G	1.7

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2026 Traco Electronic AG Specifications can be changed without notice.

Downloaded from Arrow.com.