

Specification Sheet

Part Number: 151-01245



Easy assembly without the need of a tool.

Disc covers mounting hole and minimizes ingress of dust, dirt and water.

Standard geometry fits common 6.5 mm hole size

Push Pin, Mounting Hole Dia. 6.2-7.0x12.2-13.0mm, PA66HIRHS, Black, 7000/carton

Article Number	151-01245
----------------	-----------

Type	PLUGFTOVAL
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Developed especially for the automotive industry in applications including trunks, doors, wheel housings and dash panels.
---------------------	---

Short Description	Push Pin, Mounting Hole Dia. 6.2-7.0x12.2-13.0mm, PA66HIRHS, Black, 7000/carton
-------------------	---

Global Part Name	PLUGFTOVAL-PA66HIRHSUV-BK
------------------	---------------------------

Length L (Imperial)	0.93
Length L (Metric)	23.6
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.69
Width W (Metric)	17.63
Height H (Imperial)	0.61
Height H (Metric)	15.6
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.27 x 0.47 " 0.24 x 0.48 " 0.25 x 0.50 "
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm 7.0 x 12.0 mm 6.5 x 13.0 mm 6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature intermittent, 1000 hours	+320°F (+160°C)
Operating Temperature intermittent, 5000 hours	+257°F (+125°C)
Operating Temperature intermittent, 500 hours	+329°F (+165°C)
BABA Compliant	YES
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	7000
Package Quantity (Metric)	7000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)