Aluminum Chassis *1444 Series*


Aluminum Body



Key Features:

- Spot-welded, heavy duty aluminum construction.
- Natural aluminum finish.
- Optional bottom plates are punched with 4x holes 3/16” in diameter.
- Bottom plate hardware not provided. Order separately under part number **1421J6** (Pkg. of 6x #6-32 Philips head screws).
- NOTE: our steel chassis covers (1451 series) are NOT compatible with this series.





Classic

RoHS

Photo Features





Standard version shown inside and out.



Optional bottom panels available for all sizes.



Protective covering on aluminum is perfect as a layout tool.

Accessories

- Sheet Metal Screws

Downloaded from Arrow.com.

Part Numbers

Chassis	Aluminum Thickness	Width	Depth	Height	Bottom Plate
1444-6	0.04	4.00	4.00	2.00	**1434-6**
1444-45351	0.04	4.50	3.50	1.00	**1434-4535**
1444-542	0.04	5.00	4.00	2.00	**1434-54**
1444-6415	0.04	6.00	4.00	1.50	**1434-8**
1444-8	0.04	6.00	4.00	2.00	**1434-8**
1444-643	0.04	6.00	4.00	3.00	**1434-8**
1444-12	0.04	7.00	5.00	2.00	**1434-12**
1444-753	0.04	7.00	5.00	3.00	**1434-12**
1444-772	0.04	7.00	7.00	2.00	**1434-77**
1444-9	0.04	8.00	4.00	1.00	**1434-10**
1444-10	0.04	8.00	4.00	2.00	**1434-10**
1444-84515	0.04	8.00	4.50	1.50	**1434-845**
1444-862	0.04	8.00	6.00	2.00	**1434-86**
1444-14	0.04	9.00	5.00	2.00	**1434-14**
1444-972	0.04	9.00	7.00	2.00	**1434-97**
1444-9552	0.04	9.50	5.00	2.00	**1434-955**
1444-95525	0.04	9.50	5.00	2.50	**1434-955**
1444-9553	0.04	9.50	5.00	3.00	**1434-955**
1444-1053	0.04	10.00	5.00	3.00	**1434-105**
1444-15	0.04	10.00	6.00	1.00	**1434-16**
1444-16	0.04	10.00	6.00	2.00	**1434-16**
1444-10825	0.04	10.00	8.00	2.50	**1434-108**
1444-1172	0.04	11.00	7.00	2.00	**1434-117**
1444-1273	0.04	12.00	7.00	3.00	**1434-127**
1444-22	0.05	12.00	8.00	2.00	**1434-22**
1444-12825	0.05	12.00	8.00	2.50	**1434-22**
1444-24	0.05	12.00	8.00	3.00	**1434-22**
1444-29	0.05	12.00	10.00	2.00	**1434-29**
1444-12103	0.05	12.00	10.00	3.00	**1434-29**
1444-12123	0.05	12.00	12.00	3.00	**1434-1212**
1444-1372	0.04	13.00	7.00	2.00	**1434-137**
1444-18	0.04	13.50	5.00	2.00	**1434-18**
1444-1463	0.05	14.00	6.00	3.00	**1434-146**
1444-14103	0.05	14.00	10.00	3.00	**1434-1410**
1444-1573	0.05	15.00	7.00	3.00	**1434-157**
1444-1593	0.05	15.00	9.00	3.00	**1434-159**
1444-26	0.05	16.00	8.00	2.00	**1434-26**
1444-28	0.05	16.00	8.00	3.00	**1434-26**
1444-20	0.04	17.00	4.00	3.00	**1434-20**
1444-1763	0.05	17.00	6.00	3.00	**1434-176**
1444-1773	0.05	17.00	7.00	3.00	**1434-177**
1444-1783	0.05	17.00	8.00	3.00	**1434-178**
1444-30	0.05	17.00	10.00	2.00	**1434-30**
1444-32	0.05	17.00	10.00	3.00	**1434-30**
1444-33	0.05	17.00	10.00	4.00	**1434-30**
1444-17105	0.05	17.00	10.00	5.00	**1434-30**
1444-17123	0.05	17.00	12.00	3.00	**1434-1712**
1444-17132	0.05	17.00	13.00	2.00	**1434-1713**
1444-17133	0.05	17.00	13.00	3.00	**1434-1713**
1444-17134	0.05	17.00	13.00	4.00	**1434-1713**
1444-17135	0.05	17.00	13.00	5.00	**1434-1713**
1444-17143	0.05	17.00	14.00	3.00	**1434-1714**
1444-17154	0.05	17.00	15.00	4.00	**1434-1715**
1444-17156	0.05	17.00	15.00	6.00	**1434-1715**
1444-17173	0.05	17.00	17.00	3.00	**1434-1717**
1444-17174	0.05	17.00	17.00	4.00	**1434-1717**

Tags: **chassis**, **aluminum chassis**, **classic**, **vintage**, **tube**, **audio**

Data subject to change without notice.

Downloaded from Arrow.com.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.