




**Part Number :** [152670545](#)  
**Product Description :** 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 203.00mm Cable Length, Tin (Sn) Plating, 36 Circuits  
**Series Number :** 15267  
**Status :** Active  
**Product Category :** Flat-Flexible Cable (FFC)



## Documents and Resources

### Drawings

- [152670545 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

### Specifications

- [PS-15267-001-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                            |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                                      |
| REACH SVHC         | Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)                  |
| EU RoHS            | Compliant per EU 2015/863                                                                               |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|              |                                                                                                                       |
|--------------|-----------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                |
| Category     | Flat-Flexible Cable (FFC)                                                                                             |
| Series       | 15267                                                                                                                 |
| Description  | 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 203.00mm Cable Length, Tin (Sn) Plating, 36 Circuits |
| Comments     | Contacts on the same side, Type A                                                                                     |
| Product Name | Premo-Flex FFC Jumper                                                                                                 |
| UPC          | 884982447875                                                                                                          |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A   |
| Voltage - Maximum             | 60V AC |

### Physical

|                     |               |
|---------------------|---------------|
| Cable Length        | 203.00mm      |
| Circuits (Loaded)   | 36            |
| Contact Layout Type | A (same side) |
| Design Feature      | Flexible      |

|                               |                           |
|-------------------------------|---------------------------|
| Flammability                  | 94V-0                     |
| Material - Plating Mating     | Tin                       |
| Net Weight                    | 5.355/g                   |
| Packaging Type                | Bag                       |
| Pitch - Mating Interface      | 1.00mm                    |
| Temperature Range - Operating | -40° to +105°C            |
| Termination Style             | FFC Connector             |
| Wire/Cable Type               | Flat Flexible Cable (FFC) |
| Wire Size (AWG)               | N/A                       |

---

This document was generated on Apr 29, 2026