

Data Sheet | Item Number: 811-471

Supply module; 35 mm²; for 811 Series Fuse Terminal Blocks; SCREW CLAMP CONNECTION; 35,00 mm²; light gray

<https://www.wago.com/811-471>



Color: ■ light gray

Supply module, 811 Series, screw connection

This supply module (item number 811-471) is designed for quick and simple connections. Ensure that the strip lengths are 14 mm when connecting conductors to this supply module. This product incorporates conductor terminals and utilizes a screw connection. Screw-clamp connections can handle currents from a fraction of an ampere all the way up to several hundred amperes at low to moderate frequencies. Depending on the type of conductor, this supply module is suitable for conductor cross sections ranging from 6 mm² to 35 mm².

Electrical data

Ratings per IEC/EN

Nominal voltage (III/3) 600 V

Ratings per IEC/EN 2

Rated voltage (III / 3) 1000 V

General information

Voltage type 1 AC

Voltage type 2 DC

Connection Data

Number of levels 1

Connection 1

Connection technology Screw connection

Actuation type Operating tool

Connectable conductor materials Copper

Solid conductor 6 ... 35 mm² / 10 ... 2 AWG

Stranded conductor 6 ... 35 mm² / 10 ... 2 AWG

Fine-stranded conductor 4 ... 25 mm² / 12 ... 4 AWG

Fine-stranded conductor; with insulated ferrule 4 ... 25 mm² / 12 ... 4 AWG

Strip length 14 mm / 0.55 inches

Mechanical data

Torque	4 Nm
--------	------

Material data

Note (material data)	Information on material specifications can be found here
Color	light gray
Weight	20 g

Commercial data

PU (SPU)	16 (4) pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821838654
Customs tariff number	85369010000

Product Classification

UNSPSC	39121410
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 9.0	EC002848
ETIM 10.0	EC002848
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 811-471	↓
--	-------------------

Documentation

Bid Text

811-471	19.02.2019	xml 2.51 KB	↓
811-471	28.04.2017	doc 23.00 KB	↓

CAD/CAE-Data

CAE data

EPLAN Data Portal
811-471



WSCAD Universe
811-471



1 Compatible Products

1.1 Optional Accessories

1.1.1 Jumper

1.1.1.1 Jumper



Item No.: 811-480

Jumper; 10-way; insulated; light gray



Item No.: 811-481

Jumper; 11-way; insulated; light gray



Item No.: 811-482

Jumper; 12-way; insulated; light gray



Item No.: 811-472

Jumper; 2-way; insulated; light gray



Item No.: 811-473

Jumper; 3-way; insulated; light gray



Item No.: 811-474

Jumper; 4-way; insulated; light gray



Item No.: 811-475

Jumper; 5-way; insulated; light gray



Item No.: 811-476

Jumper; 6-way; insulated; light gray



Item No.: 811-477

Jumper; 7-way; insulated; light gray



Item No.: 811-478

Jumper; 8-way; insulated; light gray



Item No.: 811-479

Jumper; 9-way; insulated; light gray

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com