# Product data sheet

Specifications



## APC NetShelter Power Cord Kit (6 ea), Locking, C13 to C14, 1.8m, North America

AP8706S-NA

## Overview

| | |
|---|---|
| **Presentation** | Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads. |

## Main

| | |
|---|---|
| **Product or component type** | Power cord |
| **Input Connection Type** | IEC 60320 C14 |
| **Cable length** | 1.82 mm |
| **Number of cables** | 6 |

## Physical

| | |
|---|---|
| **Colour** | Black |
| **Height** | 240 mm |
| **Width** | 75 mm |
| **Depth** | 55 mm |
| **Product weight** | 1.35 kg |
| **Mounting preference** | No preference |
| **mounting mode** | Not rack-mountable |

## Input

| | |
|---|---|
| **Max line current** | 10 A |
| **Input current limits** | 10 A |

## Output

| | |
|---|---|
| **Max current draw** | 10 A |
| **Number of power socket outlets** | 1 IEC 60320 C13 |
| **Power cable length** | 1.8 m |

## Conformance

| | |
|---|---|
| **Product certifications** | CSA<br>UL listed |

## Environmental

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Downloaded from Arrow.com.

| | |
|---|---|
| **Ambient air temperature for operation** | 0…105 °C |
| **Relative humidity** | 20…80 % |
| **Operating altitude** | 0...10000 ft |
| **Ambient air temperature for storage** | -25…105 °C |
| **Storage Relative Humidity** | 20…80 % |
| **Storage altitude** | 0…15240 m |

## Packing Units

| | |
|---|---|
| **Unit Type of Package 1** | PCE |
| **Number of Units in Package 1** | 1 |
| **Package 1 Height** | 24 cm |
| **Package 1 Width** | 5.5 cm |
| **Package 1 Length** | 7.5 cm |
| **Package 1 Weight** | 1.35 kg |

## Contractual warranty

| | |
|---|---|
| **Warranty (in months)** | 24 |



Downloaded from Arrow.com.

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### Environmental footprint

| | |
|---|---|
| Total lifecycle Carbon footprint | **63 kg CO2 eq.** |
| Carbon footprint of the manufacturing phase [A1 to A3] | **6 kg CO2 eq.** |
| Carbon footprint of the distribution phase [A4] | **0.1 kg CO2 eq.** |
| Carbon footprint of the installation phase [A5] | **0.6 kg CO2 eq.** |
| Carbon footprint of the use phase [B2, B3, B4, B6] | **54 kg CO2 eq.** |
| Carbon footprint of the end-of-life phase [C1 to C4] | **2 kg CO2 eq.** |
| Environmental Disclosure | **Product Environmental Profile** |

## Use Better

### Materials and Substances

| | |
|---|---|
| Packaging made with recycled cardboard | **No** |
| Packaging without single use plastic | **No** |
| EU RoHS Directive | **Compliant** |
| REACh Regulation | **Free of Substances of Very High Concern above the threshold** |
| California proposition 65 | **WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov** |
| Halogen-free status | **Product contains halogen above thresholds** |

## Use Longer

### Lifetime extension

| | |
|---|---|
| Repair | **No** |

## Use Again

### Repack and remanufacture

| | |
|---|---|
| Recyclability potential, in % | **30** |
| End of life manual availability | **End of Life Information** |
| Take-back | **No** |
| WEEE Label | **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins** |



Downloaded from Arrow.com.