## Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub







# 8P-03BMMB-SL7001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: UL1977, UL2238

You must login first for view the price

Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

## Mating Pair & Accessories

Connector Type ▾ Search



Ceres, Accessory,...
TOL-151701
N/A
− 0 +



Ceres, Accessory,...
TOL-151702
N/A
− 0 +



Ceres, Accessory,...
TOL-171801
N/A
− 0 +



M Series, M8, A...
8P-03AFFM-...
-20°C ~ +80°C
− 0 +



M Series, M8, A...
8P-03AFFM-...
-20°C ~ +80°C
− 0 +



M Series, M8, A...
8P-03AFFM-...
-20°C ~ +80°C
− 0 +

Add to Cart | Inquiry

**Specifications** | Download / CAD

| | |
|---|---|
| Nominal Current<br>**3A** | Connector Type<br>**Field Installable** |
| Shielded<br>**Plastic, Non-shielded** | No. of Contacts<br>**03** |
| Connector Gender<br>**Male** | Backshell<br>**Straight** |
| Mating Style<br>**Screw Thread** | IP Rating<br>**IP67** |
| Assembly Style<br>**Screw-in** | |

More Options

### People Also Bought



8P-03BMMB-SL7001



AB-BB03ML-BBFL-...



MSDS-04PFFC-...



M12A06FL-12AMR-...



CB-04BMMA-QL8SN0



Downloaded from Arrow.com.