



MODEL 45000 SERIES

Glass NTC Thermistors

- 100 ohm Resistance @ 25°C
- Interchangeable $\pm 0.2^{\circ}\text{C}$, 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- RoHS Compliant

FEATURES

- Glass Hermetic Seal
- 2252 to 30K Ohm Resistance @ 25°C
- Interchangeability
- Excellent High Temperature Performance
- Superior Long Term Stability
- High Sensitivity

APPLICATIONS

- High Moisture Applications
- Low to Mid Range Temperature Applications
- Tight Tolerance Instrumentation
- Use up to 250°C
- Applications Requiring Excellent Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments
- Allows use in Applications World-wide

MODEL 45000 SERIES

Glass NTC Thermistors

PERFORMANCE SPECS

	Model Number	Zero Power Resistance Ohm at 25°C	Beta 0 – 50°C (K)	Ratio Ohm 25/125°C	Maximum Working Temperature
±0.2°C Interchangeability Tolerance 0 – 70°C	45004	2252	3891	29.26	200°C
	45005	3000	3891	29.26	200°C
	45007	5000	3891	29.26	250°C
	45017	6K	3891	29.26	250°C
	45016	10K	3891	29.26	250°C
	45006	10K	3574	23.51	250°C
	45008	30K	3810	29.15	250°C

ORDERING INFORMATION

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.tlse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.