
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date BY TE CONNECTIVITY CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST
DS	-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED (ECR-14-001923)	10.FEB.'14	YH	HG
	B2	REVISED (ECR-15-005463)	09.FEB'15	YH	HG


T3 TYPE: AMBER SINGLE







EXPLODE VIEW
SCLAE 1:1












T2 TYPE: CLEAR DOUBLE







3D VIEW
SCALE 1:1

NOTE
1. GENERAL TOLERANCE: ±0.5, ±3°
2. THIS BULB HOLDER ASSY IS USED WITH:
   POSITIVE TML TE P/N 2005163-1/2
   (B2) GROUND TML TE P/N 2005164-1
   EXTENSION HSG TE P/N 2109120, 2109938

NO	SOCKET HOLE TYPE	COLOR	MATERIAL	DESCRIPTION	Q'TY			
3	-	GREY	SILICONE	O-RING	1	1	1	1
2	-	-	SUS301	LOCK PLATE	1	1	1	1
1	T2	BLACK	PA46-GF15	BULB HSG(CLEAR DOUBLE)	1	-	-	-
		NATURAL	PA46-GF15	BULB HSG(CLEAR DOUBLE)	-	1	-	-
1	T3	BLACK	PA46-GF15	BULB HSG(AMBER SINGLE)	-	-	1	-
		NATURAL	PA46-GF15	BULB HSG(AMBER SINGLE)	-	-	-	1

DESCRIPTION	P/N
BULB ASSY(CLEAR DOUBLE)-BLACK	2-2109118-2
BULB ASSY(CLEAR DOUBLE)-NATURAL	2-2109118-1
BULB ASSY(AMBER SINGLE)-BLACK	0-2109118-2
BULB ASSY(AMBER SINGLE)-NATURAL	0-2109118-1

control priority dimension ;
■ CRITICAL, ⊠ MAJOR, □ MINOR

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TE CONNECTIVITY CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±

MATERIAL -
FINISH -

DWN	YH KIM
CHK	KT LIM
APVD	HG CHO
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-

TE Connectivity

NAME
BULB ASS'Y FOR T20
(31MM EXTENSION TYPE)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2109118	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV B2


1471-9 (2/09)


Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN	APVD


(B) NEW T3 EXT













LUG LAYOUT



SECTION A-A

SECTION B-B

T3 EXT



T2 EXT

NOTE

1. MISSING DIMENSION : SEE 0-2109118-X

P/N	DESCRIPTION
6-2109118-3	BULB ASSY(AMBER SINGLE)-GREY
6-2109118-2	BULB ASSY(AMBER SINGLE)-BLACK
6-2109118-1	BULB ASSY(AMBER SINGLE)-NATURAL

NO	SOCKET HOLE TYPE	COLOR	MATERIAL	DESCRIPTION	Q'TY		
3	-	GREY	SILICONE	O-RING	1	1	1
2	-	-	SUS301	LOCK PLATE	1	1	1
1	NEW T3	(B1) GREY	PA46-GF15	BULB HSG(AMBER SINGLE)	1	-	-
1		BLACK	PA46-GF15	BULB HSG(AMBER SINGLE)	-	1	-
1		NATURAL	PA46-GF15	BULB HSG(AMBER SINGLE)	-	-	1

(B)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL –
FINISH –

DWN –
CHK –
APVD –
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –

TE Connectivity

NAME
BULB HOLDER ASS'Y FOR T-20
(31MM EXTENSION TYPE)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2109118	–

SCALE 2:1 SHEET 2 OF 2 REV B2

1471-9 (3/11)

Downloaded from Arrow.com.