
BURNDY

GAR3904, Mech Ground Conn, Conductor to Water Pipe



By Burndy
Catalog # GAR3904

Mechanical Grounding Connector, Conductor to Water Pipe, 4-4/0 AWG, 2-1/2" - 3-1/2" Pipe , 3/8" Stud

Features

- Cable clamp swivels at 90°, permits parallel grounding of one pipe on a 90° cable run for grounding several parallel pipes
- One-wrench installation for simplified installation
- Provides quality assurance to recognized industry NEC standards from an independent part

Application

For Connecting Copper Ground Conductor to Fence Posts, Water Pipe, Structural and Reinforcing Rod Shapes

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Pipe or Round Tube Size	2.5 - 3.5 in
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	4 AWG - 4/0 AWG
Conductor - Copper Str Size Range	4 AWG - 4/0 AWG
Conductor - Copper Tube Std Size Range	2 1/2-3 1/2
Conductor - Copper Tube Std Size	• 2 1/2 • 3 1/2

Dimensions

Package Height	0.000 in
Dimension - Height mm	165.1 mm
Dimension - Height inch	6.50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	4.00 in
Dimension - Width mm	152 mm
Dimension - Width inch	6.00 in
Dimension - B Length inch	1.75 in
Dimension - Length Overall inch	1.75 in

Force Related

Installation Torque Recommended in-lb	200 LBS/in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Single Conductor(GAR)
Material - Hardware	Galvanized Steel
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810234037
Type	GAR3902
U Bolt Type	1033G
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810234037
UPC 14 Digit GTIN	00781810234037

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1092
Carton Quantity	12

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.