TRACO POWER

Inductor

TCK-059

Order Code	TCK-059
Inductance	2.2 µH ±20% (at 1 kHz / 250 mV)
Impedance (DCR)	25 mΩ max.
Rated Current	4.8 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-059



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	5.2 ±0.5
B	5.8 ±0.5
C	4.5 ±0.55
D	2.3 typ.
E	5.5
F	2.15
G	1.7

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2026 Traco Electronic AG Specifications can be changed without notice.

Downloaded from Arrow.com.