THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
CMDSLC**	.10 lbs/10 Pcs [44.7 g/10 Pcs]	PHOS BRONZE
CMDSAQLC**		
CMDSLCZ**	.10 lbs/10 Pcs [44.4 g/10 Pcs]	ZIRCONIA
CMDSAQLCZ**		



NOTES:
1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR OF MODULE BASE, AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATERIALS:
   a. MODULE BASE: ABS
   b. ADAPTER HOUSING: PLASTIC
   c. SPLIT SLEEVE: SEE TABLE
   d. DUST CAP: PLASTIC
4. COMPATIBLE WITH TIA/EIA-604-10 (FOCIS-10) AND TIA/EIA-568B.3
5. DIMENSIONS IN BRACKETS ARE METRIC [mm]



REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
1	03-11-05	MC		RELEASED TO PRODUCTION	00948-17			

MINI-COM LC SENIOR/SENIOR
DUPLEX FIBER OPTIC ADAPTER MODULE
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MC
DATE: 06-26-03
CHK'D: KWR
REVIEW DRAWING NUMBERS: SEE NOTES
DRAWING FILENAME: M00948AJ_DC_00B.prt
SCALE: NONE
PART NO.: SEE TABLE
DRAWING NO.: 00948-17
SIZE: A

Downloaded from Arrow.com.