1987069-4 Product Details



Active

.100 inch AMPMODU Headers

4POS MODU II PIN HDR 90? TIN

1987069-4

TE Internal Number: 1987069-4

Product Highlights View All

- Connector
- Header Type = Breakaway
- 4 Positions
- Mating Post Length = 7.00 mm
- Row-to-Row Spacing = 2.54 mm

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

[+] Feedback

Documents | **Features** | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type	Connector
Mount Angle	Right Angle
PCB Mount Retention	Without
Board Standoff	Without
Mating Connector Lock	Without
Post Size (mm [in])	0.64 [.025]
Color	Green

Mechanical Attachment

Mounting Ears	Without
Panel Mount Retention	Without

Termination Features

Termination Post Length (mm [in])	9.10 [0.358]

Dimensions

Mating Post Length (mm [in])	7.00 [0.276]

Body Features

Header Type	Breakaway
Row-to-Row Spacing (mm [in])	2.54 [0.100]
Selectively Loaded	No
Mount Type	Printed Circuit Board

Contact Features

Contact Plating, Mating Area, Material	Tin
Solder Tail Contact Plating	Tin over Nickel
Contact Shape	Square
Contact Base Material	Copper Tin

Housing Features

Housing Material	PBT GF

Configuration Features

Number of Positions	4
Number of Rows	1
Surface Mount Compatible	No

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

High Temperature Housing	No

Operation/Application

High Speed Serial Data Connector	No

Other

Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.