

© 2020 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING FORMAT	08MAY2020	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inch]

TE PN: 412200-000

OUTSIDE WOUND (BACK SLIT LEFT)
LABEL ACROSS: 1
PER ROLL QTY: 30.48m / 100 feet

MATERIAL	POLYVINYL FLUORIDE (TEDLAR®)
ADHESIVE TYPE	PERMANENT ACRYLIC
LINEAR	BROWN KRAFT

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	−0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL: SEE TABLE

FINISH: GLOSS

DWN 12MAY2020 GOPALAKRISHNA HV
CHK 12MAY2020 D.BURGAT
APVD 12MAY2020 D.BURGAT
PRODUCT SPEC: TTDS−005
APPLICATION SPEC: –
WEIGHT: 159g

TE Connectivity

NAME: TEDLAR® LABEL – YELLOW – CONTINUOUS 38.1mm x 30.4m (1.5inch x 100ft)
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	FB1U7	C-TTVF150YW−100	–

CUSTOMER DRAWING

SCALE	SHEET	REV
NTS	1 OF 1	A1

TTVF150YW−100

1471−9 (1/15)

Downloaded from Arrow.com.