| Rev | AWO # | Description | Date | Appr |
|---|---|---|---|---|
| - | | RELEASED | 1/18/10 | |

APPROVED: _____

DATE: _____ TITLE: _____




RECOMMENDED PCB LAYOUT
(TOP VIEW)

**SPECIFICATIONS:**

Material:
Body: Hi-temp thermoplastic, rated UL 94V-0
Contacts: Bronze, Gold plated.
Electrical:
Operating voltage: 25 VAC max
Current rating: 0.3 Amps max
Contact resistance: 35 mohms Max.
Insulation resistance: 1000 mohms min.
Dielectric withstanding voltage: 250 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +85°C
Environmental:
Lead free, RoHS compliant.
Recommended soldering temp: 260°C for 5 sec

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM
TOLERANCES: EXCEPT AS NOTED

| DIMENSIONS | | ANGLES |
|---|---|---|
| .X | ± .38 | ± 3° |
| .XX | ± .25 | |
| .XXX | ± .20 | |

| APPROVALS | | DATE |
|---|---|---|
| DRAWN | DY | 1/18/10 |
| CHECKED | | |
| APPROVED | | |


**ADAM TECH**
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710


TITLE: SO DIMM SOCKET, 204 PIN, SMT
1.5V DRAM, 9.2MM HEIGHT

| SIZE | PART NO. | REV. |
|---|---|---|
| X | SOD-204-S-4-9.2 | - |

REF: S00127T | SCALE: NTS | SHEET 1 OF 2

Downloaded from Arrow.com.