**Part Number :** 191930081
**Product Description :** VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton
**Series Number :** 19193
**Status :** Active
**Product Category :** Ring and Spade Terminals
**Engineering Part Number :** BB-337-08T



## Documents and Resources

### Drawings

191930081_sd.pdf

### Specifications

PS-19902-011-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19193 |
| Description | VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton |
| Keyword | Ring Terminal, Ring Terminals |
| Product Name | VersaKrimp |
| Style | Ring |
| Type | Ring Terminal, Metric Ring Terminal |
| UPC | 800753039094 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Physical

| | |
|---|---|
| Barrel Type | Closed - Brazed |
| Insulation | None |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Net Weight | 0.453/g |
| Packaging Type | Adhesive Tape on Reel |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Stud Size | 8 (M4) |
| Temperature Range - Operating | -50° to +149°C |

Downloaded from Arrow.com.

| | |
|---|---|
| Termination Interface Style | Crimp or Compression |
| Wire Size (AWG) | 14, 16 |
| Wire Size $mm^2$ | 2.50-1.50 |

## Application Tooling

### Global

| Description | Part Number |
|---|---|
| ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press | 190270068 |
| Mini-Mac Applicator, Air Feed Mylar Tape | 638853900 |



Downloaded from Arrow.com.