Johanson Part Number LRC0402CS4N3GV001T

Johanson Part Number: LRC0402CS4N3GV001T	Johanson Company: JTI
Legacy P/N: L-07C4N3SV6T	Size for Capacitors (EIA): None
Description: Ceramic Inductor, 0402, 4.3nH±0.3nH, 300mA, Ni/Sn (RoHS), Orientation Mark Full Marking, 7" Reel Paper Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.024
Schedule B: 8504.50.40.00	Thickness (Min): 0.016
ITAR: No	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.013
RoHS Compliance: Yes, RoHS 10/10	Standard Item: No
REACH: Yes	Lead Time Typical (Weeks)*: 17
Country of Origin: TW	Length (Min): 0.035
Product Family: Inductors	Length (Max): 0.043
Product Subfamily: Ceramic Inductors	Width (Min):0.016
Capacitance Value: None	Width (Max): 0.024
Cap Unit of Meas: None	Part Weight (mg): 0.98
Tolerance: ±0.3nH	Packaged Width (lb) Arm: 0.30
Voltage: None	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: None	Packaging Qty: 10000
Termination: 0	Operating Temp Range: 100000000
Marking: Orientation Mark Full Marking	Storage Temp Range (Packaged): -10°C to +40°C
Product Release Date: Jan. 3, 2006	Storage Temp Range (None Operating): -40°C to +125°C
Harmonization: 8504.50.40.00	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: https://www.johansontechnology.com/ceramic-inductors

Printed from: https://www.johansontechnology.com/part/LRC0402CS4N3GV001T/

Downloaded from Arrow.com.