Part Number : 393730008
Product Description : 7.50mm Beau Eurostyle Right-Angle PCB Header, Closed Ends, 8 Circuits
Series Number : 39373
Status : Active
Product Category : Terminal Blocks and Barrier Strip
Engineering Part Number : MX-CIM089P3-0N



Documents and Resources

Drawings

393730008_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39373
Description	7.50mm Beau Eurostyle Right-Angle PCB Header, Closed Ends, 8 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822348042111

Agency

UL	E48521

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black

Downloaded from Arrow.com.

Entry Angle	N/A
Flammability	94V-0
Lock to Mating Part	No
Net Weight	25.000/g
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
PCB Retention	No
PC Tail Length	3.50mm
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	110°C
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
7.50mm Beau Eurostyle Pluggable Terminal Blocks	39371
7.50mm Beau Eurostyle Pluggable Terminal Blocks	39374

Downloaded from Arrow.com.