© 20 BY - . a TE Connectivity Ltd. company. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASE	30JUN2020	SZ	SZ
	A1	ADDED NEW DASH NUMBER -6	12JAN2026	CZ	LM

NOTES,UNLESS OTHERWISE SPECIFIED

1.MATERIAL:

HOUSING - THERMOPLASTIC, GLASS PREINFORCED, COLOR, BLACK, UL 94V-0

CONTACTS- COPPER ALLOY.

2.FINISH:


MATING AREA - NOBLE METAL OVERALL NICKEL.

SOLDER TAIL - MATTE TIN OVERALL NICKEL.


3 MARK P/N AND DATA CODE IN APPROX. AREA AS SHOWN.

4 OPTIONAL FEATURE BASE ON SPECIFIC PART NUMBER, SEE THE TABLE FOR DETAIL


5 NO TOOLING.





POST FEATURE: NO
KEY FEATURE: NO




POST FEATURE: YES
KEY FEATURE: YES







SECTION S-S



A6,B6	NO	YES	13.97	13.97	3.50	/	25.40	12.70	30.18	/	30.48	33.48	11	11	2358256-6	
NO	NO	YES	34.29	36.83	3.50	/	60.96	30.48	65.74	/	66.04	69.04	25	25	2358256-5	
NO	NO	NO	/	/	2.50	/	60.96	30.48	65.74	/	66.04	69.04	25	25	2358256-4	
NO	YES	NO	/	/	3.50	17.78	17.78	8.89	22.56	17.78	22.86	25.86	8	8	2358256-3	5
NO	YES	YES	34.29	36.83	3.50	60.96	60.96	30.48	65.74	60.96	66.04	69.04	25	25	2358256-2	5
NO	NO	NO	/	/	3.50	/	60.96	30.48	65.74	/	66.04	69.04	25	25	2358256-1	
OMITTED PINS	POST 4	KEY 4	DIM K	DIM J	DIM H	DIM G	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	N	M	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.5
2 PLC ±0.25
3 PLC ±0.10
4 PLC ±
ANGLES ±

MATERIAL -

FINISH -

DWN SEAN ZHANG 11JUN2019
CHK -
APVD SUNY ZHAO 11JUN2019
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME SINGLE BEAM CARD EDGE RIGHT ANGLE


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	-	C-2358256	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 2 | REV A1


Downloaded from Arrow.com.

© 20 BY - . a TE Connectivity Ltd. company. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED MATING BOARD EDGE CONFIGURATION
(PRIMARY SIDE SHOWN)



RECOMMENDED MOUNTING BOARD CONFIGURATION LAYOUT
VIEW FROM COMPONENT SIDE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.10
2 PLC ±0.05
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: TBD -
FINISH: - -

DWN SEAN ZHANG 11JUN2019
CHK -
APVD SUNY ZHAO 11JUN2019
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME: SINGLE BEAM CARD EDGE RIGHT ANGLE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	-	C-2358256	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 2 OF 2 | REV A1

4805 (3/13)

Downloaded from Arrow.com.