BURNDY

YAV25LNK, Cu Compression, 1-Hole, 3/8" Stud, 1/0 AWG, Nickel Plated

By Burndy
Catalog # YAV25LNK

Uninsulated Ring Terminal For 1/0 AWG (Nickel Plated)

Features

- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service
- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance, and excellent ductility for crimping
- Double thick tongue provides a structurally strong terminal tongue
- Produced from tubular copper, extra copper material assures the ompression terminal will operate cooler than the conductors it connects
- Internally beveled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion

Application

For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Aircraft Size	AN 0
Conductor - Copper Str Aircraft Size Range	AN 0
Conductor Size	1/0 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Package Height	0.000 in
Dimension - Hole Size mm	10 mm
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	3/8 in
Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	2.03 in
Dimension - D inch	0.85 in
Dimension - N inch	0.42 in

General

Die Index	43
Trade Name	HYLUG™
Sub Brand	TERMINALS, HYLUG
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Type	Ring Tongue
UPC 14 Digit GTIN	00781810085813
Material	Copper
Plating Type	Nickel
UPC	781810085813

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Downloaded from Arrow.com.

Pallet Quantity	39200

Product Assets

Catalog [English]

A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.