


031-0033-0001 Product Details



031-0033-0001
(1467936-1)

TE Part Number: 1467936-1

✔ Active

🔖 Add to Part List

SMB RF Connectors

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

Product Highlights:

- Connector
- Jack
- Miniature
- Terminate To Coaxial Cable
- Coupler Style = Threaded

[View all Features](#) | [Find Similar Products](#)

💬 Live Product Chat

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [BULKHEAD JACK 'D' MOUNT S-50 SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- [Screw-On Series Straight Solder Plugs and Jacks with...](#) (PDF, English)

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Gender](#) = Jack
- Connector Series = Miniature
- [Body Style](#) = Straight
- [Grade](#) = Commercial
- Safety Wire Holes = Without
- Thread Size = 4.83 [.190]-32
- Panel Thickness (mm [in]) = 3.56 [0.140]
- Body Material = Brass
- Dielectric Material = TEFLON

Mechanical Attachment:

- [Panel Attachment](#) = With
- [Panel Attachment Style](#) = Rear Mount
- Panel Attachment Method = Lockwasher and Nut

Electrical Characteristics:

- [Connector Impedance \(\$\Omega\$ \)](#) = 50
- Environmental Seal = Without
- Solderless = No

Termination Related Features:

- [Coaxial Cable Termination Type](#) = Solder

Body Related Features:

- Coupler Style = Threaded
- [Pin Protection](#) = Without
- Solder Lug = Without
- [Body Plating](#) = Silver
- Cable Jacket Diameter (mm [in]) = 2.24 [0.088]

Contact Related Features:

- [Center Contact Plating](#) = Gold
- Contacts = With

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- [Terminate To](#) = Coaxial Cable

Other:

- Brand = Microdot