



| DATE | REV | ECN | APP'D. BY |
|---|---|---|---|
| 5-22-15 | A4 | 10337 | TRM |
| 3-8-16 | A5 | 10596 | TRM |
| 7-14-23 | B0 | 12209 | JE |
| | | | |




P.C.B. RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE

ALL CENTERLINE DIMENSIONS ARE BASIC

NOTES:

1. CONNECTOR MATERIALS:
   HOUSING: THERMOPLASTIC UL94 V-0
   CONTACTS: COPPER ALLOY
   CONTACT PLATING: SELECTIVE GOLD IN CONTACT AREA
   SEE CHART FOR PART NUMBER
2. FOR PRODUCT SPECIFICATIONS SEE PR022-01.
3. DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.

| 30 MICRO-INCHES [0.76um] | SS-641010-A-NF-A111 |
|---|---|
| CONTACT PLATING IN MATING AREA | PART NUMBER |

RoHS

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°

SHEET NO. 1 OF 1


stewart CONNECTOR a bel group

11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512
http://www.stewartconnector.com


TITLE: TEN CONTACT, TEN POSITION, SHORT VERSION JACK


THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/


| DRN BY: | KRL | DATE | 1/30/06 |
|---|---|---|---|
| APPD BY: | JM | DATE | 1-31-06 |
| DWG NO. | CT640205 | REV. | B0 |


Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.