MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED. MFG. CODE 81929

SWITCH – TOGGLE FLUSH KEY

CATALOG LISTING
2TP201-50

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CIRCUIT DIAGRAM



ELECTRICAL DATA

L192 10A 125, 250, 277 VAC
1/4HP 125 VAC,
1/2HP 250, 277 VAC
3A 125 VAC "L"

NOTES

1 CIRCUIT DESIGNATION AND MICRO SWITCH CAT. LIST. STAMPED ON SIDE OF SWITCH

2 THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F

3 SCREWS FURNISHED UNASSEMBLED

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED. TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04		
ONE PLACE	X.X	0.4/.016	X.X	0.8/.03
TWO PLACES	X.XX	0.15/.006	X.XX	0.38/.015
THREE PLACES			X.XXX	0.13/.005
ANGLES				

DESIGN UNITS SI METRIC ☐ US CUSTOMARY ☒

WEIGHT

DRAWING NUMBER 2TP201-50 PAGE 1 OF 1
ISSUE M 6
RELEASE NO. PR-10585 REPLACES

REVISIONS
A C056164 J A P 6 MAR 85
B C057496 CJH 25 SEP 85
C C058717-B WJK 23 OCT 86
C C060369 WJK 10 NOV 86
D CO-94413 J J A 8 OCT 99
E 202714 CSL 3 APR 01

RASTER FO-52854-C
DRAWN JEF 23 OCT 81
CHECK CEB 25 FEB 82
CHECK KJC 23 JAN 82
CHECK

Downloaded from Arrow.com.