



Automotive Parts > Automotive Connectors > Automotive Housings > Timer Connector Housing



Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **21**

Sealable: **No**

Operating Temperature Range: **-30 – 100 °C [-22 – 212 °F]**

Number of Rows: **3**

[All Timer Connector Housing \(436\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	No
Primary Locking Feature	On the Terminal
Connector System	Wire-to-Board, Wire-to-Wire

Configuration Features

Number of Positions	21
Number of Rows	3

Electrical Characteristics

Nominal Voltage Architecture	24 V
------------------------------	------

Body Features

--	--



Primary Product Color	Gray
Connector & Keying Code	A

Contact Features

Contact Size	2.8mm
Contact Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Contact Current Rating (Max)	30 A

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	Yes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Product Length	36.2 mm[1.425 in]
Connector Height	26.5 mm[1.043 in]

Usage Conditions

Operating Temperature Range	-30 – 100 °C[-22 – 212 °F]
Operating Temperature (Max)	100 °C[212 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Serviceable	No
Connector Position Assurance Capable	No

Compatible Parts



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB

TE Part # 1-927768-1
JPT REC 2.8 Contact SRC Au




TE Part # 8-968975-2
MCP2.8 GEH ASSY 21P


TE Part # 1719810-1
JPT REC 2.8 Contact SRC Sn



TE Part # 8-968975-1
MCP2.8 GEH 21P



TE Part # 3-966140-6
MESSERLEISTE 21P



TE Part # 967635-1
2.0 KONT

Also in the Series | Junior Power Timer



Automotive Connector Locks & Position Assurance(8)



Automotive Housings(279)



Automotive Seals & Cavity Plugs(8)



Automotive Signal & Power Connector Housings(275)




Other Automotive Connector Accessories(3)


Customers Also Bought



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #2-967624-6
JUN-POW-TIM GEH 18P



TE Part #1-967625-3
JUN-POW-TIM GEH 21P



Documents

Product Drawings

JUN-POW-TIM GEH 21P

English

CAD Files

Customer View Model

ENG_CVM_1-967625-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_1-967625-2_D.3d_stp.zip

English

Customer View Model

ENG_CVM_1-967625-2_D.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English