
Part Number : 386007803
Product Description : 6.35mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, with Clamp Washer Screws, 300V, 3 Circuits
Series Number : 38600
Status : Obsolete
Product Category : Terminal Blocks and Barrier Strip
Engineering Part Number : 60503-C-50



Obsolete

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	38600
Description	6.35mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, with Clamp Washer Screws, 300V, 3 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Fixed Mount Barrier
Type	Barrier Strips
UPC	800756247380

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	33.000/g
Number of Rows	1
Orientation	Horizontal
Panel Mount	No

Obsolete

Downloaded from Arrow.com.

PCB Thickness - Recommended	3.18mm
PC Tail Length	5.10mm
Pitch - Mating Interface	N/A
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	No
Shrouded	Tri-Barrier
Stackable	No
Temperature Range - Operating	-40° to +130°C
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.33-0.82

Solder Process Data

Lead-Free Process Capability	WAVE

Obsolete

Downloaded from Arrow.com.