

Part Number : 369210410
Product Description : KK Plus 396-to-KK Plus 396 Off-the-Shelf (OTS) Cable Assembly, 3.96mm Pitch, Single Row, 1000.00mm Length, 4 Circuits, Black
Series Number : 36921
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

369210410_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	36921
Description	KK Plus 396-to-KK Plus 396 Off-the-Shelf (OTS) Cable Assembly, 3.96mm Pitch, Single Row, 1000.00mm Length, 4 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	KK Plus 396-to-KK Plus 396
Product Name	KK Plus
Type	Discrete Wire Assembly
UPC	193264110773

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V DC

Physical

Cable Length	1000.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Female

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	68.398/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Size (AWG)	18

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK Plus 396 Vertical Unshrouded Headers	207478
KK Plus 396 Vertical Shrouded Headers	207479

Downloaded from Arrow.com.