

COIL:

RESISTANCE	700 Ω ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
MUST RELEASE	1.5 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 5 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: DIELECTRIC - 1000 VRMS EXCEPT 500 VRMS ACROSS OPEN CONTACTS

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMP/28 VDC RESISTIVE 50,000 OPERATIONS

DR. R.B. 1-30-91 CK. 1/30/91 JMB

Communications Instruments, Inc.

CUST. C.I.I. STD

CUST. NO.

TYPE "C" RELAY

CEW-1C-24A

SUPERSEDED
NOT the LATEST REVISION

Downloaded from Arrow.com.