


C-HVSLS800082X1XX

REV	ECN	DESCRIPTION	DATE	MODIFIED
1		PRE-RELEASE	Sep-27-16	

CUSTOMER DRAWING







TECHNICAL DATA	
CURRENT RATE 25MM^2 WIRE	120A
CURRENT RATE 35MM^2 WIRE	150A
CURRENT RATE 50MM^2 WIRE	180A
VOLTAGE RATE	1000V DC
OPERRATING TEMPERATURE	-40-125°C
DIELECTRIC WITHSTANDING VOLTAGE	3000V AC
INSULATION RESISTANCE	2000MΩ
DURABILITY	50 CYCLES
SHIELDING	YES
WATERPRROF(MATED CONDITION)	IP67 IP6K9K
CORROSION-PROFF GRADE(SALT FOG TEST)	96 HOURS
AMBIENT TEMPERATURE	-40-70°C


C-HVSLS800082X1XX

C-HVSLS800082X1XX

DIMENSIONS	TOLERANCES	PROJECTION		TITLE
ANSI Y14.5M UNITS: MM Pro/E FILE	.X ±0.5 .XX ±0.30 ANGLES ±0.5°		Amphenol Pcd Shenzhen ENGR Tom Dai Sep-27-16	HVSLS800 PLUG RA
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN		CHKD APPD	SIZE A3 / DWG NO. C-HVSLS800082X1XX / REV 1
				CODE: 58982 / SCALE: 1:1 / SHEET 1 OF 15

Downloaded from Arrow.com.

CUSTOMER DRAWING



C4220053603	50mm^2 BELLOWS GAP	C422005360X
C4220053602	35mm^2 BELLOWS GAP	
C4220053601	25mm^2 BELLOWS GAP	
C4220053583	50mm^2 END GAP	C422005358X
C4220053582	35mm^2 END GAP	
C4220053581	25mm^2 END GAP	
C4270052003	50mm^2 CABLE SEAL	C427005200X
C4270052002	35mm^2 CABLE SEAL	
C4270052001	25mm^2 CABLE SEAL	
HVSLS8000850	50mm^2 PIN CONTACT RA	HVSLS80008XX
HVSLS8000835	35mm^2 PIN CONTACT RA	
HVSLS8000825	25mm^2 PIN CONTACT RA	
HVSLS80008B	B KEY	HVSLS80008X
HVSLS80008A	A KEY	
P/N	DESCRIPTION	REMARK

Notes :
Number 2-7 assembly for the client


INDEX	P/N	DESCRIPTION	QTY	REMARK
7	/	BELLOWS	2	THE CUSTOMER'S
6	/	CABLE	2	THE CUSTOMER'S
5	C422005360X	BELLOWS GAP(波纹管盖)	2	
4	C422005358X	END GAP(尾盖)	2	
3	C427005200X	CABLE SEAL(线缆密封圈)	2	
2	HVSLS80008XX	PIN CONTACT RA(公针)	2	
1	HVSLS80008X	ASSEMBLE PLUG RA(弯头主体)	1	ASSEMBLE


SIZE	DWG NO.	REV
A3	C-HVSLS800082X1XX	1
CODE: 58982	SCALE: 7:10	SHEET 2 OF 15

C-HVSLS800082X1XX
C-HVSLS800082X1XX


Downloaded from Arrow.com.

CUSTOMER DRAWING








HVSLS80008A



HVSLS80008B







P/N:HVSLS80008X(弯头主体)

SIZE	DWG NO.	REV
A3	C-HVSLS800082X1XX	1
CODE: 58982	SCALE: 1:1	SHEET 3 OF 15

C-HVSLS800082X1XX

C-HVSLS800082X1XX

Downloaded from Arrow.com.