

Products → Low Voltage Products and Systems → Connection Devices → Markers and Marking Systems
→ Terminal Block Markers

General Information

Extended Product Type:	PROCAP6
Product ID:	1SNK900612R0000
EAN:	3472599097438
Catalog Description:	PROCAP6 Protecting cap for SAT6 labels
Long Description:	- Easily protect your Self Adhesive sTrip SAT, - Quickly put it on the terminal blocks: PROCAP delivered in strip of 10 parts

Ordering

Color:	Transparent
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160013D0201
Instructions and Manuals:	1SNK160027C0205

Dimensions

Product Net Width:	6 mm
Product Net Height:	12 mm
Product Net Length:	2.4 mm
Product Net Depth / Length:	2.4 mm
Product Net Weight:	0.8 g

Technical

Spacing:	6 mm
Function:	Protecting cap
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polycarbonate

Suitable For:

CDK4
CDS4
CDS4-R1
ZDK4-22
ZDS4-22-R1
ZK10
ZK10-PE
ZK16
ZK16-PE
ZK2.5-SF
ZK2.5-SF-R
ZK2.5-S-R1
ZK4
ZK4-3P
ZK4-4P
ZK4-PE
ZK4-PE-3P
ZK4-PE-4P
ZK6
ZK6-3P
ZK6-PE
ZK6-PE-3P
ZS4-PE-R2
ZS4-R2
ZS4-SF
ZS4-SF-R
ZS4-SF-T
ZS4-SP-R1
ZS4-SP-T2-R1
ZS4-S-R1
ZS4-S-R2
ZS4-S-T-R1
ZS6
ZS6-3S
ZS6-3S-PE
ZS6-4S
ZS6-4S-PE
ZS6-D1
ZS6-D1-PE
ZS6-D2
ZS6-D2-PE
ZS6-PE
ZS6-S
ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225156C1000
Environmental Information:	1SND220061E1000
Instructions and Manuals:	1SNK160027C0205
RoHS Information:	1SND230504F0204

Classifications

Object Classification Code:	X
E-number:	2967975
ETIM 4:	EC000761 - Labelling for terminal block
ETIM 5:	EC000761 - Labelling for terminal block
ETIM 6:	EC000761 - Labelling for terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	158 mm
Package Level 1 Depth / Length:	243 mm
Package Level 1 Gross Weight:	0.016 kg
Package Level 1 EAN:	3472599097438
Package Level 2 Units:	10000 piece
Package Level 3 Units:	320000 piece
Product Packing Type:	Bag

