RoHS2

- Product Numbers by Series
- Part Number Configuration

LF07WBJ-6P

Product	LF07WBJ-6P
Series	LF
Connector Type	Jack
Rated Current	2 A
Rated Voltage (AC)	AC 30 V
Rated Voltage (DC)	DC 42 V

Detailed Specifications

Last Updated On Oct. 30, 2017

Product information	
Part No.	LF07WBJ-6P
CL No.	CL0136-2001-2-00
Basic information	
Connector Type	Jack
Rated Current	2 A
Rated Voltage (AC)	AC 30 V
Rated Voltage (DC)	DC 42 V
Number of Positions	6
Operating Temperature	-25 to 85 ℃
Water Resistance	IP 68
Withstanding voltage	300 V Max.
Locking Style	Bayonet
Wire Termination Method	Soldering
Cable Outer Diameter	5 mm
Mating/Unmating Cycles	1000
Finger Protection	No

Downloaded from Arrow.com.

Download
DRAWING(2D)
DRAWING(3D)
more
ADD TO MY LIST
CONTACT US
Browsing History

Series: LF
Product: LF07WBJ-6P

Metal Shields	Yes
Contact Plating	Gold
Salt Spray Test Duration (Corrosion Resistance)	48 h
Shell Material	Metal

- Mechanical Specifications
- Dimensional Information
- Packaging Specifications

Download

Catalog	Product Series Catalog	DOWNLOAD
Data Sheet	Drawing (2D)	DOWNLOAD
	3D Model (IGES)	DOWNLOAD
	3D Model (STEP)	DOWNLOAD
	Specification Sheet	DOWNLOAD

*I need help with a product or information

© 1999-2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

Downloaded from Arrow.com.