# Datasheet for part number TR1823RMS1NB

| Our Catalog Part Number: TR1823RMS1NB |
|---|
| Our Global Manufacturing Part Number: 192990-1350 |
| Brand: Cannon Product Category: Trident Product Line: Trident Series: TR |

| Product Datasheet | |
|---|---|
| Series | Trident Ringlock |
| Connector Type | Receptacle for Flange Mounting |
| Environmental Sealing | unsealed |
| Sealing Methode | no sealing |
| Shell Size | 18 |
| Contact Quantity | 23 |
| Contact Gender | Pin |
| Contacts included | No, order separately |
| Operating Voltage | 48 Vac, 60 Vdc |
| Current Rating | Up to 13 A |
| Operating Temperature | -55°C to +105°C |
| Insulator Resistance | 5000 Megaohms at 500 V dc |
| Durability | Up to 500 Mating Cycles |
| Flammability | UL94-V0 |
| Salt Spray | 48 hours |
| Vibration | 10 g's peak, 10 to 500 Hz, 9 hours |
| Physical Shock | 50 g's peak, 11msec., half-sine pulse |
| Insulator Material | Black Nylon |
| Coupling Nut Material | Nickel Plated Zinc Alloy |
| Sealing Grommet Material | Silicone Rubber |
| Mounting Style | Standard |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.