37000800430 - 370 Series



Series: 370

Questions? Contact Littelfuse Support

Fuse 370 Datasheet

The 370 Series are TR5®, sub-miniature, fast-acting type, 250V rated fuses, designed in accordance to IEC 60127- 3.

Features:

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free

Check Stock

Order Samples

Feedback

Electrical Characteristics | Technical Resources | Environmental Info

Property (Mouseover for details)	Value
Ampere Rating (A)	0.08
Nominal Melting I^2T (A^2sec)	0.0014
Interrupting Rating	35A@250VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	120
Nominal Voltage Drop (mV)	370
Nominal Cold Resistance (Ohms)	2
Opening	Fast-Acting (F)
Package Size	TR5 (8.5x8mm)
VAC (V)	250

Littelfuse, Inc. 8755 West Higgins Road Suite 500, Chicago, IL, A, 773-628-1000 Copyright © 2017 Littelfuse, Inc.

Downloaded from Arrow.com.