

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-24-253847	29FEB2024	WH	LC
	B	REVISED PER ECR-26-278377	23JUL2026	TL	JH

D

C

B


A

D




C

B

A




- 1 MATERIAL: HOUSING: PBT,UL94 V-0.
TERMINAL: BRASS,2.0μm MIN TIN OVER 1.25μm MIN NICKEL OVERALL.
- 2 CONTACT SOLDERTAIL KINK DIRECTION(BOARLOCK) SEE BELOW TABLE.
3. PART COLOR VARIES IN TINT AND MAY APPEAR UNEVENLY MIXED
4. RECOMMENDED MATING PART:[]-2406060-[] OR []-2406093-[]
5. PACKAGING: LOOSE PIECE




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. HUO	19JUN2023	TE Connectivity		
DIMENSIONS:		CHK L. CHEN	20JUN2023			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. ZHANG	20JUN2023	NAME HEADER ASSEMBLY, WITH BOSS COLOR, VERTICAL, SINGLE ROW EP2.5		
mm		PRODUCT SPEC	108-2418			
0 PLC ±- 1 PLC ±0.4 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±3°		APPLICATION SPEC	114-13315	SIZE A2	CAGE CODE 00779	DRAWING NO C-2464099
MATERIAL		WEIGHT	-	RESTRICTED TO -		
1		CUSTOMER DRAWING		SCALE N/A	SHEET 1 OF 2	REV B


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-




2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




RECOMMENDED PCB LAYOUT



7 POSITION



8 POSITION



17.50	20.83	22.50	8	5-2464099-8	4-2464099-8	3-2464099-8	2-2464099-8	1-2464099-8	2464099-8
15.00	18.33	20.00	7	5-2464099-7	4-2464099-7	3-2464099-7	2-2464099-7	1-2464099-7	2464099-7
12.50	15.83	17.50	6	5-2464099-6	4-2464099-6	3-2464099-6	2-2464099-6	1-2464099-6	2464099-6
10.00	13.33	15.00	5	5-2464099-5	4-2464099-5	3-2464099-5	2-2464099-5	1-2464099-5	2464099-5
7.50	10.83	12.50	4	5-2464099-4	4-2464099-4	3-2464099-4	2-2464099-4	1-2464099-4	2464099-4
5.00	8.33	10.00	3	5-2464099-3	4-2464099-3	3-2464099-3	2-2464099-3	1-2464099-3	2464099-3
2.50	5.83	7.50	2	5-2464099-2	4-2464099-2	3-2464099-2	2-2464099-2	1-2464099-2	2464099-2
DIM.C	DIM.B	DIM.A	POS.	IVORY	GREEN	YELLOW	BLACK	BLUE	RED
PART NO									

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN W. HUO	19JUN2023		 TE Connectivity												
				CHK L. CHEN	20JUN2023														
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD D. ZHANG		20JUN2023		NAME									
		0 PLC ±-				PRODUCT SPEC		HEADER ASSEMBLY, WITH BOSS COLOR, VERTICAL, SINGLE ROW EP2.5											
		1 PLC ±0.4																	
		2 PLC ±0.25																	
		3 PLC ±-																	
		4 PLC ±-				APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
		ANGLES ±3°				114-13315		A2		00779		C-2464099		-					
		FINISH				WEIGHT													
						-													
CUSTOMER DRAWING								SCALE		N/A		SHEET		2 OF 2		REV		B	