



PRODUCT-DETAILS

TBM0750  
MEDIUM WALL 3:1 ADH.LINED



| General Information    |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type: | TBM0750                                                                                                                                               |
| Product ID:            | 7TCA017410R0007                                                                                                                                       |
| EAN:                   | 5414363109419                                                                                                                                         |
| Catalog Description:   | MEDIUM WALL 3:1 ADH.LINED                                                                                                                             |
| Long Description:      | Heat Shrink Tubing, Rated for 600 Volts, 90 Degree C, Continuous Use, RoHS Compliance, 19.1mm Expanded, 5 Per Bag, Black, Medium Wall, Adhesive Liner |
| Display Name:          | TBM0750                                                                                                                                               |

| Ordering                 |               |
|--------------------------|---------------|
| E-Number (Finland):      | 5240646       |
| EAN:                     | 5414363109419 |
| UPC:                     | 786210082660  |
| Minimum Order Quantity:  | 5 piece       |
| Country of Origin:       | Canada        |
| Selling Unit of Measure: | each          |

## Container Information

|                                 |                    |
|---------------------------------|--------------------|
| Package Level 1 Units:          | 5 piece            |
| Package Level 1 EAN:            | 5414363109419      |
| Package Level 2 Units:          | 35 piece           |
| Package Level 2 Width:          | 6.7 in<br>170 mm   |
| Package Level 2 Height:         | 6.7 in<br>170 mm   |
| Package Level 2 Depth / Length: | 51.2 in<br>1300 mm |

## Additional Information

|                             |                                  |
|-----------------------------|----------------------------------|
| Brand / Label:              | Shrink-Kon                       |
| Color:                      | Black                            |
| Effective Date:             | 19991216                         |
| Flammability Hazard Rating: | Flame Retardant                  |
| Process Temperature Rating: | -67 to +230 °F<br>-55 to +110 °C |
| Product Main Type:          | TUBING AND BOOTS                 |
| Product Name:               | PLASTIC CONDUIT                  |
| Shrink Ratio:               | 3:1                              |
| Shrink Temperature:         | 248 °F<br>120 °C                 |

## External Classifications and Standards

|                                     |                              |
|-------------------------------------|------------------------------|
| ETIM 7:                             | EC000217 - Shrink tubing     |
| ETIM 8:                             | EC000217 - Shrink tubing     |
| ETIM 9:                             | EC000217 - Shrink tubing     |
| ETIM 10:                            | EC000217 - Shrink tubing     |
| UNSPSC:                             | 39121723                     |
| IDEA Granular Category Code (IGCC): | 5073 >> Heat shrinkable tube |

## Material Compliance

|                                              |                                                                        |
|----------------------------------------------|------------------------------------------------------------------------|
| RoHS Information:                            | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |
| REACH Information:                           | False - does not contain substances > 0.1 mass percentage              |
| WEEE Category:                               | Product Not in WEEE Scope                                              |
| Conflict Minerals Reporting Template (CMRT): | 9AKK108472A2584                                                        |

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Wire Management and Connectivity > Identification & Heat Shrink > Tubing and Boots

