Part Number : 469921010
Product Description : Mini-Fit Jr. Receptacle Housing, Dual Row, Nylon 6/6 UL 94V-2, 10 Circuits, Glow-Wire Capable, Black
Series Number : 46992
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

469921010_sd.pdf

PK-5557-002-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

55560001-AS-000.pdf

55560002-AS-000.pdf

PS-45750-001-001.pdf

PS-5556-001-001.pdf

457500003-TS-000.pdf

55560001-TS-000.pdf

55560010-TS-000.pdf

TS-5556-002-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(ethane-1,2-

Downloaded from Arrow.com.

	diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	46992
Description	Mini-Fit Jr. Receptacle Housing, Dual Row, Nylon 6/6 UL 94V-2, 10 Circuits, Glow-Wire Capable, Black
Application	Wire-to-Board, Wire-to-Wire
Component Type	Receptacle
Product Name	Mini-Fit Jr.
UPC	887191637860

Agency

CSA	LR19980
UL	E29179

Physical

Downloaded from Arrow.com.

Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.353/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Dual Row Plug Housings	46993
Mini-Fit Jr. Right-Angle Dual Row Reflow Solder Capable Headers	46991

Use with Part(s)

Description	Part Number
Mini-Fit Female Crimp Terminals	5556
Mini-Fit Plus Female Crimp Terminals	45750

Downloaded from Arrow.com.