




Quality Products. Service Excellence.

Deep Hinged Window Kits 1481WDH Series



Features

- Extra deep kits are designed to provide protection and easy access to components and equipment installed inside an enclosure.
- Frame is 14 gauge mild steel or 316L stainless steel.
- Maintain environmental protection level of enclosure. Painted mild steel maintain Type 4 and 12. Stainless Steel maintain Type 4, 4X and 12.
- Quarter turn latch for easy access.
- 2.5 inches of extra usable depth
- Oil resistant neoprene gasket ensures a watertight seal.
- Hinges can be oriented in any direction.
- Window is 0.25" thick, UV Resistant Polycarbonate.
- Conveniently sized to allow mounting on the door of any Hammond Wallmount Series enclosure, or in any other Hammond enclosure with a suitable mounting surface.
- Mounting hardware and template are included.
- Finished in ANSI 61 gray recoatable powder or natural brushed stainless steel.



Painted Steel Part No.	316 Stainless Steel Part No.	Overall Dimensions		Viewing Area		Latch Qty	Maximum Cut-Out Size
		A	B	C	D		
1481WDH1418 ¹	1481WSSDH1418 ²	12.19	14.56	8.00	9.17	1.00	9.19 11.56
1481WDH1612 ¹	1481WSSDH1612 ²	14.19	8.14	10.00	2.75	1.00	11.19 5.14
1481WDH1620 ¹	1481WSSDH1620 ²	14.19	16.14	10.00	10.75	1.00	11.19 13.14
1481WDH1624 ¹	1481WSSDH1624 ²	14.19	20.14	10.00	14.75	1.00	11.19 17.14
1481WDH2016 ¹	1481WSSDH2016 ²	18.19	12.14	14.00	6.75	1.00	15.19 9.14
1481WDH2024 ¹	1481WSSDH2024 ²	18.19	20.14	14.00	14.75	1.00	15.19 17.14
1481WDH2416 ¹	1481WSSDH2416 ²	22.19	12.14	18.00	6.75	1.00	19.19 9.14
1481WDH2420 ¹	1481WSSDH2420 ²	22.19	16.14	18.00	10.75	1.00	19.19 13.14
1481WDH2430 ¹	1481WSSDH2430 ²	22.19	26.14	18.00	20.75	1.00	19.19 23.14

Painted Steel	316 Stainless Steel	Overall Dimensions		Viewing Area		Latch	Maximum	
Part No.	Part No.	A	B	C	D	Qty	Cut-Out Size	
1481WDH3024 ¹	1481WSSDH3024 ²	28.19	20.14	24.00	14.75	2.00	25.19	17.14
1481WDH3624 ¹	1481WSSDH3624 ²	34.19	20.14	30.00	14.75	2.00	31.19	17.14

¹ UL/ CSA Type 12 and Type 4

² UL/ CSA Type 12, Type 4 and Type 4x

Tags: **window, window kit, polycarbonate, deep, Type 4, Type 4X, Type 12, stainless**

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.