

ECM-EHL

Intel® Celeron®/Atom™ Elkhart Lake SoC 3.5" Micro Module

- Intel® Celeron®/Atom™ Elkhart Lake SoC BGA Processor
- Bottom Layer Soldered Processor
- 1 x SODIMM socket supports up to 32GB DDR4 3200MTs SDRAM
- Supports 3 Independent Displays
- M.2 B-Key, M.2 E-Key, uSIM Card Slot
- 4 x COM Ports
- 2 x USB 3.1 Gen 2 (10Gbps), 4 x USB 2.0
- 2 x Intel® I226-LM 2.5GbE Ethernet Controllers
- Select SKU supports Extended Temperature -40°C ~ 85°C
- +9~36V Wide Range DC Input

Specification Download Ordering Info

Model Name	Description
ECM-EHL-J6413	3.5" SBC, Intel® Celeron J6413 1.8GHz Quad Core, Fanless, 2 x LAN, 4 x COM, 6 x USB, 8-GPIO, +9V~+36V, 0~60C
ECM-EHL-X13E	3.5" SBC, Intel® Atom™ x6413E 1.5GHz Quad Core, Fanless, 2 x LAN, 4 x COM, 6 x USB, 8-GPIO, +9V~+36V, -40~85C
ECM-EHL-X25RE	3.5" SBC, Intel® Atom™ x6425RE 1.9GHz Quad Core, Fanless, 2 x LAN, 4 x COM, 6 x USB, 8-GPIO, +9V~+36V, -40~85C

Contact us at BCMSales@bcmcom.com or give us a call 949-470-1888

Understand more about our Custom Industrial Motherboards and Open Frame Tablets

Explore ODM/OEM Services

Not finding what you are looking for?

Providing detail descriptions and your company's email address will help us providing the best solution for you!

How Can We Help?

Company *

Name *

First Last

Business Email Address *

Country/Region *

Please enter your State or Country (if outside the United States)

Message Details *

Submit

News Release & Trade Show | Product Guide | Tech Center

CONTACT BCM

BCM Advanced Research
11 Chrysler, Irvine, CA, 92618 USA
BCMSales@bcmcom.com

© BCM Advanced Research. All Rights Reserved. Privacy Policy | Legal Notice | Sitemap

Downloaded from Arrow.com.