
Part Number : 936010219
Product Description : Heavy-Duty Screw Terminal Insert, Male, 6-Pole, 35A, Numbered 1-6, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7306.6141.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Screw Terminal Insert, Male, 6-Pole, 35A, Numbered 1-6, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»
Component Type	Inserts - Screw Terminal
Insert Series	S-HSB
Product Name	Heavy-Duty Connectors
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191877273

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	35.0A
Voltage - Maximum	830V
Wire Protection	Yes

Physical

Component Size	16B «77X27»
Durability (mating cycles max)	500
Gender	Male
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate

Downloaded from Arrow.com.

Material - Plating	Silver
Net Weight	79.000/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	6
Stripping Length	10.50mm
Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	1.20 Nm
Wire Size (AWG)	10-20
Wire Size mm^2	0.50-6.00

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Screw Terminal Insert, Female, 6-Pole, 35A, Numbered 1-6, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»	936010211

Use with Part(s)

Description	Part Number
Use With	Size 16B «77x27» Hoods and Housings

Downloaded from Arrow.com.