

 PRODUCTS ▾

 DISTRIBUTOR INVENTORY

 INDUSTRIES ▾

 SUPPORT ▾

 NEWS & EVENTS ▾

 ABOUT US ▾

64AT11-7E

Products > Switches > Toggle Switches > AT Series > **64AT11-7E**

Overview

MICRO SWITCH AT Series Toggle Switch, 4 pole, 3 position, Solder T2 type terminal, Locking Lever.

MICRO SWITCH AT toggle switches provide a compact

[View More](#)



 view all 64AT11-7E literature

 view distributor inventory

 sample request

 email support


 get support

 email sales

 find a distributor

 email this page

Technical Specifications

Product Type	MICRO SWITCH Toggle	Ampere/Voltage Range (Resistive Load)	0.1 A to 7.0 A at 0.5 Vdc to 28 Vdc								
Circuitry	4PDT	Action	3 position								
Circuitry/Operating action	<table><tr><td>Pole 1&2</td><td>Keyway Position</td><td>Center Position</td><td>Opposite Position</td></tr><tr><td>Pole 3&4</td><td>C-NO</td><td>C-NC</td><td>C-NO</td></tr></table>	Pole 1&2	Keyway Position	Center Position	Opposite Position	Pole 3&4	C-NO	C-NC	C-NO	Mounting	Bushing 15/32 in
Pole 1&2	Keyway Position	Center Position	Opposite Position								
Pole 3&4	C-NO	C-NC	C-NO								
Termination	Solder T2 type	Lever Lock	 E Locked in center position								
Comment	FAA-PMA approved	Availability	Global								

[View More](#)

View documents in: 

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 64AT11-7E highres photo	Photo	English	2MB
 64AT11-7E lowres photo	Photo	English	189KB
 AT Series Toggle Switch Assemblies	Catalog Information	English	427KB
 Sensors and Switches in Oil Rig Applications	Application Note	English	7MB

[View More](#)

Product Features

- Gold or silver contacts
- Choice of sealed bushing
- Standard or pull to unlock toggle lever
- Short behind-panel depth
- Solder or quick connect termination
- 2,4, 6, or 8 SPDT precision basic switches
- 2 or 3 position, momentary or maintained action

Applications

- Industrial machinery and equipment
- Military and commercial aviation

- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

- HOME PAGE
- PRODUCTS
- DISTRIBUTOR INVENTORY
- INDUSTRIES
- SUPPORT
- NEWS & EVENTS
- ABOUT US

DISTRIBUTOR LINKS

- ECOM LOGIN
- LEARN CENTER
- REQUEST ACCESS TO ECOM
- SALES/AD PORTAL LOGIN
- SALES/AD PORTAL ACCESS REQUEST
- SAMPLE REQUEST
- SUPPLIER MICROSITE

LANGUAGE

English 

SOCIAL MEDIA**SITE INFORMATION**

- PRIVACY STATEMENT
- SITEMAP

TERMS & CONDITIONS

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.