

Packaging Number

IMSA-11600S-20Y900

Category:	FFC/FPC Connectors
Series:	11600

Drawings

Product 2D:	PDF ↓
Packaging 2D:	PDF ↓
Product Spec:	PDF ↓

Product Details

Floating:	No
Connection Orientation:	Straight/Vertical
Pitch:	0.5
Pin Count:	20
Plating:	Gold
Mount:	SMT
Boss Type:	Non
Vacuum Tape Included:	No
Terminal Material:	Corson
Part Height:	6.5
Base	
Base Number:	A
Mold Material:	LCP
Packaging Type:	Tape
Environmental	
Beryllium & Halogen Free:	Yes
Advanced	
Rating Voltage AC / DC:	50 volts/ 50 volts
Current Rating:	0.5A
High Speed:	No
Data Transfer Rate (Gbps):	3.0

Downloaded from Arrow.com.

Inquire About This Product

*Full Name**

*Email Address**

IMSA-11600S-20Y900

*Message**

Get Started

Related Technologies

Auto I-Lock

Automatic locks make single action assembly easy and reliable.

Learn More

I-Lock

IRISO's unique "I-LOCK" technology prevents accidental cable removal.

Learn More

Downloaded from Arrow.com.

Copyright © 2020 IRISO Electronics CO., LTD, All Rights Reserved.

Downloaded from Arrow.com.