| ITEM NO. | PART NUMBER | DESCRIPTION | QTY. | COMPONENT NOTES |
|---|---|---|---|---|
| 1 | 50-00988 | Connector, 5 pin M12 A-code plug, 12xL22mm, gold plated, molding style, solder cup, IP67, shielded | 1 | |
| 2 | 30-01586 | Wire, 5C TS, 22 AWG, UL20387, 300V, 105C, 60C oil, UV, 6.5 mm, shielded, VW-1, PVC, 80A, black | 1 | |
| 3 | 24-00361 | Overmold, M12 plug and jack, 90° | 1 | PVC, black |
| 4 | Heat Shrink | Heat shrink, black | 1 | covers drain |
| 5 | Heat Shrink | Heat shrink, black | 1 | covers end of jacket |




**Notes:**
Cable rated for 60 V, 4 A
Temperature: -40 ~ 105 °C
Oil resistant up to 60 °C
Water resistant up to 75 °C
UV resistant

IP67 waterproof rating when mated with corresponding (IP67) connector

Functionally equivalent components may be substituted



Front View
Not to Scale

| Wiring Diagram | |
|---|---|
| 50-00988 | wire color |
| 1 | red |
| 2 | yellow |
| 3 | black |
| 4 | white |
| 5 | blue |
| Shell | shield/drain |

| Revision: | Date: | Description: |
|---|---|---|
| A | 12/30/2021 | Initial release |
| | | |
| | | |
| | | |
| | | |

Prepared: PB Digitally signed by PB Date: 2022.01.25 11:45:35 -08'00'

Verified: MP Digitally signed by MP Date: 2022.01.25 13:54:59 -08'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:

RoHS compliant

Function test: no open, no short circuit, no intermittent

Description:

Cable, 10000 mm, 1.0 mm 5C 90° 50-00988 M12 plug to 5 mm tinned, 22 AWG, 30-01586 wire, shielded


TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com


Size: A

Part number: 10-04739

Scale: 1:1

Sheet 1 of 1


To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com


5 4 3 2 1


Downloaded from Arrow.com.