ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00399	Connector, mono plug, 3.5xL23.5 mm, brass, nickel plated, molding style	1	
2	30-00177	Wire, 2C BC, 28 AWG, 300V, 80C, 3.8 mm, foil + shield, PVC	1	
3	24-00028	Overmold, PVC, black	1	black



Notes:
Cables individually tied and bundled in groups of 10

Functionally equivalent components may be substituted

Wiring Diagram	
50-00399	wire color
tip	red
sleeve	white

Revision:	Date:	Description:
A	5/24/2010	Initial release
A1	10/6/2011	Updated specification
A2	3/28/2012	Updated wire part number
A3	10/9/2014	Updated connector
A4	10/21/2016	Corrected wiring diagram

Prepared: GL Digitally signed by GL Date: 2016.10.28 12:19:47 -07'00'

Verified: DN Digitally signed by DN Date: 2016.10.28 15:29:01 -07'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:

RoHS compliant

Function test: no open, no short circuit, no intermittent

Description:

Cable, 1830 mm, 3.5 mm 50-00399 slim mono plug to 5 mm tinned, 28 AWG, 30-00177, shielded

TENSILITY

tel 1.541.323.3228 *800* 877.670.7118
fax 1.541.323.4202 *web* tensility.com

Size: A

Part number: 10-00344

Scale: 1:2

Sheet 1 of 1

5 4 3 2 1

Downloaded from Arrow.com.