



Part Number : [192210378](#)

Product Description : Compression Style Ring
Tongue Terminal for 1 AWG Cable, Stud Size 3/8" (M9),
Unplated, Carton

Series Number : 19221

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : BCL-138



Documents and Resources

Drawings

[192210378 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19901-017-001.pdf](#)

[PS-19902-017-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP: |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19221 |
| Description | Compression Style Ring Tongue Terminal for 1 AWG Cable, Stud Size 3/8" (M9), Unplated, Carton |
| Comments | Heavy Duty |
| Keyword | Ring Terminal, Ring Terminals |
| Product Name | Battery Cable Lug |
| Style | Ring, Unplated |
| Type | Battery Cable Lug |
| UPC | 800753064331 |

Agency

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

Physical

| | |
|---------------------------|----------|
| Barrel Type | Closed |
| Insulation | None |
| Material - Plating Mating | Unplated |
| Net Weight | 13.245/g |

| | |
|-----------------------------|----------------------|
| Packaging Type | Carton |
| Stud Size | 3/8" (M9) |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | N/A |
| Wire Size (AWG) | 1 |

Application Tooling

Global

| Description | Part Number |
|---|------------------|
| Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG | <u>192840034</u> |
| Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices | <u>192860117</u> |
| Die Set (Large) for the HHLS Hydraulic Crimper | <u>192900011</u> |
| Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals | <u>192940008</u> |
| Square "DIN" style dies for 2 AWG | <u>640037970</u> |

This document was generated on Dec 25, 2025