

Home → Tool Types → Insert Bits → Security Torx® Insert Bit 10 Pack

Security Torx® Insert Bit 10 Pack



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Security Torx Size	Pack Quantity	Price	Qty
70127	Security Torx® Insert Bit T7s x 25mm 10pk	T7s	10 Bits		0
70128	Security Torx® Insert Bit T8s x 25mm 10pk	T8s	10 Bits		0
70129	Security Torx® Insert Bit T9s x 25mm 10pk	T9s	10 Bits		0
70168	Security Torx® Insert Bit T40s x 25mm 10pk	T40s	10 Bits		0
70135	Security Torx® Insert Bit T10s x 25mm 10pk	T10s	10 Bits		0
70142	Security Torx® Insert Bit T20s x 25mm 10pk	T20s	10 Bits		0
70148	Security Torx® Insert Bit T25s x 25mm 10pk	T25s	10 Bits		0
70160	Security Torx® Insert Bit T27s x 25mm 10pk	T27s	10 Bits		0

SKU	Product	Security Torx Size	Pack Quantity	Price	Qty
70163	Security Torx® Insert Bit T30s x 25mm 10pk	T30s	10 Bits		0
70139	Security Torx® Insert Bit T15s x 25mm 10pk	T15s	10 Bits		0

Add to Cart

Add to Wishlist

Share on Facebook

Tweet This

Pin it

We accept

Details

Wiha premium bits - exact fit precision machined
Universal fit for all standard bit holders & power tools
Wiha special chrome-vanadium-molybdenum tool steel
Torx is a 100% improvement in drive performance over other systems
Virtually eliminates screw head cam-out
Through hardened for best wear resistance
Security Bits can also be used as regular Torx Bits

Additional Info

Head Type	security torx
Country of Manufacture	Germany
Pack Quantity	10 Bits
Bit Drive Size	1/4" Hex
Bit Length	25mm~1"
ISO Standard Size	C6.3
Coating	Standard
Machine Hardness	HRC 59-61
Material	Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

You may also be interested in the following product(s)

Security Torx 3.5" power blades

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter

[Subscribe](#)

© 2017 Wiha Tools USA. All Rights Reserved.

SHIPS FREE

