Part Number : 2002185300
Product Description : Hand Crimp Tool for MultiCat Machined Mid-Power Contact, 28-20 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

2002185300-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for MultiCat Machined Mid-Power Contact, 28-20 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	MultiCat
Tool Type	Hand Crimp Tool
UPC	193264021666
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Applicable Parts

Description	Part Number
MultiCat Mid-Power Crimp Terminal, Male, 0.20µm Gold Plating, 24-20 AWG	2029351000
MultiCat Mid-Power Crimp Terminal, Male, 0.20µm Gold Plating, 28-26 AWG	2029352000
MultiCat Mid-Power Crimp Terminal, Male, 1.30µm Gold Plating, 24-20 AWG	2029353000
MultiCat Mid-Power Crimp Terminal, Male, 1.30µm Gold Plating, 28-26 AWG	2029354000
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 24-20 AWG, with Sleeve	2029360100
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 28-26 AWG, with Sleeve	2029360200
MultiCat Mid-Power Crimp Terminal, Female, 0.20µm Gold Plating, 24-20 AWG, without Sleeve	2029361000
MultiCat Mid-Power Crimp Terminal, Female, 0.20µm Gold Plating, 28-26 AWG, without Sleeve	2029362000
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 24-20 AWG, without Sleeve	2029363000
MultiCat Mid-Power Crimp Terminal, Female, 1.30µm Gold Plating, 28-26 AWG, without Sleeve	2029364000

Downloaded from Arrow.com.