


Home → Tool Types → Torque Screwdrivers → EasyTorque Nm Screwdriver Handles

Quickly see and find recommended torque blades for this handle

EasyTorque Nm Screwdriver Handles



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Price	Qty
29205	Easy Torque SF Handle 4.4 in lbs/0.5Nm		0
29206	Easy Torque SF Handle 5.3 in lbs/0.6Nm		0
29209	Easy Torque SF Handle 8.0 in lbs/0.9Nm		0
29211	Easy Torque SF Handle 9.7 in lbs/1.1Nm		0
29212	Easy Torque SF Handle 10.6 in lbs/1.2Nm		0
29214	Easy Torque SF Handle 12.4 in lbs/1.4Nm		0
29220	Easy Torque SF Handle 17.7 in lbs/2.0Nm		0

SKU	Product	Price	Qty
29225	Easy Torque SF Handle 22.1 in lbs/2.5Nm		0
29230	Easy Torque SF Handle 26.6 in lbs/3.0Nm		0
29238	Easy Torque SF Handle 33.6 in lbs/3.8Nm		0
29241	Easy Torque SF Handle 35.4 in lbs/4.0Nm		0
29245	Easy Torque SF Handle 39.8 in lbs/4.5Nm		0
29251	Easy Torque SF Handle 44.2 in lbs/5.0Nm		0

Add to Cart

- Add to Wishlist
 Share on Facebook
 Tweet This
 Pin it

We accept



Details

EN ISO 6789, BS EN 26789, ASME B107.14M
 Each Tool Factory Preset and Calibrated No Certificate of calibration
 Latest Ergonomic SoftFinish multi-component handle enables optimal power transmission
 Audible and perceptible click when the pre-set torque has been attained
 Guaranteed Torque Accuracy of $\pm 10\%$ to 5000 cycles / 1 year
 50% greater loosening torque
 Mechanism insensitive to industrial lubricants
 Automatically resets for next torque cycle

Additional Info

Country of Manufacture	Germany
TorqueControl Type	Pre-Set easyTorque
Handle Grip Types	SoftFinish - cushioned
Torque Display Scale	Dual Nm and Inch lbs

WRITE YOUR OWN REVIEW


Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)