



Part Number : [3003634011](#)
Product Description : MX150 Mid-Voltage Mat-Sealed Female Connector Assembly, Single Row, 4 Circuits, 48V, Keying Option A, with Connector Position Assurance, Light Blue
Series Number : 300363
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

- [3003634011 sd.pdf](#)
- [PK-31300-903-001.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [AS-33472-100-001.pdf](#)
- [AS-33472-100-CH-001.pdf](#)
- [AS-33472-100-FR-001.pdf](#)
- [PS-33471-000-001.pdf](#)
- [PS-33471-000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per

	D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	300363
Description	MX150 Mid-Voltage Mat-Sealed Female Connector Assembly, Single Row, 4 Circuits, 48V, Keying Option A, with Connector Position Assurance, Light Blue
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Comments	with Connector Position Assurance (CPA)
Product Name	MX150
UPC	196823526909

Physical

Circuits (maximum)	4
Color - Resin	Blue (Light)

Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	9.400/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Designed to mate with EWCAP interface 150-S-004-1-Z03

Use with Part(s)

Description	Part Number
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>

This document was generated on Apr 15, 2026